




NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. PLEASE REFER TO PRODUCT DOCUMENTATION FOR FURTHER INFORMATION.
3. UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLITERS (INCHES).
4. MOUNTING BUTTON IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLESS MOUNT FOR 3RD PARTY ENCLOSURE.
BUTTON IS PROVIDED WITH THE UNIT. DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND IN THE PROVIDED MANUAL.
5. BRACKET KITS TO MOUNT TO SPECIFIC 3RD PARTY ENCLOSURES ARE AVAILABLE AS OPTIONS.
6. LENGTH OF THE CORDIS 30000MM-/-70MM
7. DIMENSION TOLERANCE: LENGTH /~3MM, WIDTH +/-1MM, DEPTH +/-0.5MM
8. REFER TO THE TABLE FOR DETAIL CORD LENGTH DEFINITION



Drawing Maker:	Eva Lin	June 12. 2017
Design Engineer:	Siang_H	June 12. 2017
Approver:	Tom_H	June 12, 2017



DO NOT SCALE DRAWING SHEET 1 OF 1

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF RARITAN, Inc. AND SHALL NOT BE COPIED, REPRODUCED OR USED, IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM RARITAN, Inc. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

TITLE: iPDU Zero U

Three Phase, 16A/380-415V Plug Type: IEC60309 16A 3PY Outlet Type: C13 (24)

MPX3-5514U M5 & MPX3-4514U M5

REV. PX3-5514U & PX3-4514U PX3-5514U-M5 & PX3-4514U-M5 2B